



*The #1 Specified Holiday Detector Around the World*

# MODEL AP/W Holiday Detector

## 800v to 35,000v

**NEW BATTERY!**  
**Longer Life**  
**Light Weight**



### Features:

- 800 volts to 35,000 volts
- T&R Safety Switch
- Integrated Voltmeter
- Ergonomic Design
- Audio & Visual Holiday Indicators



*Instrument will work only when safety handle is depressed.*

Distributed by:

[teststations.com](http://teststations.com)

[detectron.com](http://detectron.com)

**[Info@tinker-rasor.com](mailto:Info@tinker-rasor.com) | [tinker-rasor.com](http://tinker-rasor.com)**

Tinker & Rasor quality is found in our products, our people and our customer service.

# TINKER & RASOR

## PRODUCT DATA SHEET | MODEL AP/W HOLIDAY DETECTOR

### FEATURES:

- 800 v to 35,000 volts in one instrument
- Safety Switch Feature
- Integrated Voltmeter
- Audible and Visual Holiday Indicators
- Military -style, locking PowerPak cable
- Ergonomic design, reduces user fatigue
- Portable, belt worn unit
- Lightweight, long life Rechargeable battery

### CONSTRUCTION:

- Rugged injection molded resin case
- Longer PowerPak cable
- Form fitting design for wearing on hip or over the shoulder

### APPLICATIONS:

- Check coatings on:
  - Pipelines
    - Internal
    - External
  - Tanks
  - Concrete
  - Sewers
  - Manholes

### RECOMMENDATIONS:

Specified and Approved on specs around the world  
Conforms to NACE International SP0188, SP0274, SP0490 and others

### ENVIRONMENT:

-10°C to 50°C (14°F to 122°F)

### DIMENSIONS:

Shipping / Carrying Case:  
41" x 18" x 8", 35lbs  
(1040mm x 457mm x 203mm, 15.87kg)  
Instrument:  
6.75" x 8.5" x 3.5", 8 lbs  
(171.5mm x 216mm x 89mm, 3.62kg)

**DELIVERY:** **Immediately from STOCK**  
ExWorks New Braunfels, TX USA

**SERVICE:** **24-hour Turn-Around**

**TERMS:** Net 30 Days, on approval of credit

**WARRANTY:** **3 Years**, parts and labor



### KIT INCLUDES:

- Instrument and Battery
- PowerPak and 5' Cable
- Ground Cable, 20'
- Wand and Extension Handles
- Battery Charger Belt
- Electrode\*
- Carrying Case
- Instructions

\* Choose an electrode to include with the kit:

Full Circle Spring Electrode for any one pipe diameter between 2" and 36" **or**

Half Circle Spring Electrode for any one pipe diameter between 0.75" and 8" **or**

Silicone-Rubber Brush Electrode with any one width between 2" and 8"



**One PowerPak  
Does It All!**

**Full range of  
voltages in one  
instrument.**

**AVAILABLE FROM STOCK**

**tinker-rasor.com**